

## Stainless Steel Vertical Screw Auger Conveyor

Mfg:

Model:

Stock No. BBCF162.8

Serial No.:

Stainless Steel Vertical Screw Auger Conveyor. Screw dimensions: 8 in. dia. x 16 ft. L. Housing diameter: 9 in. Flight pitch: 8 in. Shaft diameter: 2 in. Reliance Electric Motor, 5 hp, 1160 rpm, 230/460 V, 15.6/7.8 amps, 60 Hz, 3 phase. Driver pulley diameter: 6 in. Driven pulley diameter: 19 in. Inlets: (1) 10 in. dia. Outlets: (1) 10 in. W x 10 in. H discharge. Overall dimensions: 20 ft. 3 in. L x 2 ft. 1 in. W x 3 ft. H.









