

## Frick High Pressure Horizontal Receiver – 575 Gallon

Mfg: Frick

Model:

Stock No: BDBS07

Serial No:

Frick High Pressure Horizontal Receiver Tank. National Board: 68711. Approximate capacity: 575 gallons. Inside straight-wall dimensions: 36 in. dia. x 10 ft. 1-½ in. L. Refrigerant: R-717 (ammonia). MAWP: 250 psig at -20° F to 200 °F. Inlets/Outlets: (1) 4 in. dia. port, (1) 2 in. dia. port, (4) 1/2 in. dia. ports. Overall dimensions: 12 ft. 10 in. L x 3 ft. 3 in. W x 5 ft. 2 in. H.



