

1992 Trane Condensing Unit - 60 Ton

Mfg: Trane

Model: RAUCC604BF03D1

Stock No. ACEU20

Serial No. J92K83556

1992 Trane Condensing Unit- 60 Ton. Model: RAUCC604BF03D1. S/N: J92K83556. Refrigerant: R-22. Design pressure: 460 psig. Test pressure (hi/lo): 450/300 psig. Power supply: 460 V, 60 Hz, 3 phase. Minimum ckt ampacity: 123 amps. Maximum fuse size: 125 amps. (4) Trane 3-D Scroll Compressors, 460 V, 26.3 RLA, 142 LRA, 60 Hz, 3 phase. (6) 26+ diameter direct drive, propeller type fans. (6) Fan motors, 1 hp each, 460 V, 1.8 amps, 60 Hz, 3 phase. (2) condenser coils 3 rows of 12 fins per inch. Inlets: (2) 2 in. dia. refrigerant discharge copper ports. Outlets: (2) 3/4 in. dia. refrigerant discharge copper ports. In addition to allowing the orbiting scrolls to touch in all three dimensions and form completely enclosed compression chambers, the Trane 3-D Scroll compressors offer very smooth and low torque compression cycles thus reducing wear and eliminating the need for pistons, connecting rods, wrist pins and valves. Also standard on this model are: spring isolators and a suction service valve. Overall dimensions: 9 ft. 6 in. L x 7 ft. 5 in. W x 6 ft. 8 in. H.



