

1994 Multistack / Thermal Care Chiller Package

Mfg: Thermal Care/Mayer

Model: MS50BH12W / TMW50

Stock No. ACEU76

Serial No.

1994 Multistack / Thermal Care Chiller Package. Model: MS50BH12W / TMW50. (2) 24 ton Bristol compressors. Model: H2NG294DPEF. Compressor #1: S/N: 16797030899; Compressor #2: S/N: 27000007972. Refrigerant: R-22. 460 V, 60 Hz, 3 phase, 200 LRA. (2) 1994 Plate heat exchangers certified by SWEP AG, Type: B45 x 060. Plate heat exchanger #1: S/N 29406-16060-0077. Plate Heat Exchanger #2: S/N 29406-16060-0054. MAWP: 368 psi @ 365 °F, MDMT: -319 °F @ 346 psi. Plate pack dimensions: 6 in. L x 9-1/2 in. W x 20-1/2 in. H. Inlets/outlets: (2) 6-1/2 in., (2) 3 in., (2) 2 in. Overall dimensions: 62-1/2 in. L x 57 in. W x 63 in. H. The units are industrial design water or brine chillers utilizing scroll type compressors. The package is good for process chilling out of the range of an off the shelf unit and has water regulating valves for low condenser water temperature. This package can operate as a single unit or with two different solutions, if necessary. Capacity will vary based on conditions, but the unit is approximately 50 tons. (ACN456).





CERTIFIED BY SWEP AG
 MAWP : 368 PSI AT 365 °F
 MDMT : -319 °F AT 346 PSI
 SERIAL NO : 29406-16060-0077
 YEAR OF MANUFACTURE : 1994
 TYPE : B45 x 060



PART NO 700515-16-1783 MADE IN USA
 SERIAL NO 18797030899
 MODEL NO H2NG294DPEF
 W/C 420
 LRA 200
 V- 460 HZ 60 PH 3
 V- 380/415 HZ 50 PH 3
 LRA 215
 CE
 BRISTOL

CERTIFIED BY SWEP AG
 MAWP : 368 PSI AT 365 °F
 MDMT : -319 °F AT 346 PSI
 SERIAL NO : 29406-16060-0054
 YEAR OF MANUFACTURE : 1994
 TYPE : B45 x 060
 SWEP
 TILINGEN
 SWITZERLAND

PART NO 700515-1802-00
 MODEL NO H2NG294DPEF OC-16
 (S)27000007972
 (P)COMPRESS23
 CE
 BRISTOL
 V- 460 HZ 60 PH 3
 LRA 200
 V- 380/415 HZ 50 PH 3
 LRA 215