

Sullair Ammonia Screw Compressor Package – 200 HP

Mfg: Sullair

Model: C16LA717-3.7

Stock No: BNCA156.9

Serial No: 056-01290

Sullair Ammonia Screw Compressor Package. Model: C16LA717-3.7. S/N: 056-01290. Capacity: 119 tons of R-717 with a 10°F suction temperature and a 95°F condensing temperature. Lincoln electric motor, 200 HP, 3565 rpm, 460 V, 60 Hz, 3 phase. E.L. Nickell oil separator, Nat'l Bd: 1537, S/N: 14-7852B, MAWP: 300 psi @ 250°F, Shell thickness: 0.250, head thickness: 0.256, inside straight wall dimensions: 1 ft. 9 in. dia. x 5 ft. 7 in. L. 1999 API Basco Oil Cooler, S/N: 5996239-101, shell side MAWP: 300 psi @ 300°F, shell side MDMT: 20°F @ 300 psi, tube side MAWP: 150 psi @ 300°F, tube side MDMT: 20°F @ 150 psi. Displacement: 445 cfm. Vi setting: 3.7. Connections: 5 in. suction and 3 in. discharge. Sullair Control Panel, Model: C16LA717-3.7, S/N: 056-01290. Max press: NH3-300psig. Inlets: (2) 2 in. dia. port, (1) 6 in. dia. port. Outlets: (1) 4 in. dia. flanged port, (1) 2 in. dia. port. Weight: 5100 lbs. Overall dimensions: 11 ft. L. x 4 ft. 3 in. W. x 7 ft. 9 in. H. Compressor runtime: 8,879.1hrs. (ACN331-BC/Motor-81).





