

Stainless Steel Screw Auger Conveyor

Mfg:

Model:

Stock No. BBCF164A.15

Serial No.:

Stainless Steel Screw Auger Conveyor. Screw dimensions: 12 in. dia. x 14 ft. L. Housing diameter: 1 ft. 1 in. Flight pitch: 8 in. Shaft diameter: 2 in. Sterling Electric Motor, 2 hp, 1200 rpm, 220/440 V, 5.8/2.9 amps, 60 Hz, 3 phase. Inlets: (1) 10 in. L x 10 in. W infeed. Outlets: (1) 1 ft. 1 in. dia. discharge. Overall dimensions: 15 ft. x 11 in. L x 1 ft. 6 in. W x 2 ft. 9 in. H.





MFGR.	STERLING		
TYPE	FR.	H.P. 2	
V.	220/440	AMP. 8.8/2.3	
CY.	30	RPM	1200 PH. 3
SER.			
MOD.			