

Unused Fristam FKL-150 Positive Displacement Pump - 10 HP

Mfg: Fristam

Model: FKL150

Stock No.: CAGC1037

Serial No.: FKL1501003403

Unused Fristam rotary lobe positive displacement pump. Model FKL-150. Serial FKL1501003403. Max pressure: 500 PSI. Max speed 600 RPM. Displacement per revolution: 0.259 gallons. Max flowrate: 155.4 gallons per minute at 600 RPM. Baldor-Reliance Super-E Washdown motor: 10 HP, 208-230/460V, 25.4-24/12 amps, 1770 RPM, 215TC frame, 60 Hz, 3-phase. Nord gear reduction drive 11.71 ratio (151 final RPM, 39 GPM). Stainless steel base. Ports:3 in. clamp. Condition is unused, never run. (ACN115)





