

Frick Recirculating Tank – 38 in. Dia. x 11 ft. L

Mfg: Frick

Model:

Stock No: BDBS03

Serial No: 261826

Frick Recirculating Tank. Serial no: 261826 National Bd. no: 68839. Approximate capacity: 700 gallons. Refrigerant: R-717 (Ammonia). MAWP: 150 psi @ -20°F to 200°F. (2) Cornell pumps, model: 2CBS2-4, with Marathon electric motors: 2 hp, 1740 rpm, 230/460V, 60 Hz, 3 phase. Frick PRR control panel. Hansen Technologies Variable-Level® LB3 control panel. Henry Valve Co. LI-49, sight glass. (2) Cyrus Shank safety relief valves, type: 803 TD. Overall Dimensions: 12 ft. 8 in. L x 7 ft. W x 10 ft. 5 in. H.





