

Sullair Ammonia Screw Compressor – 200 HP

Mfg: Sullair

Model: C16LA717-3.7

Stock No: BNCA157.9

Serial No: 006-84000006

Sullair Ammonia Screw Compressor. Model: C16LA717-3.7. S/N: 25964CGF. Capacity: 119 tons of R-717 with a 10°F suction temperature and a 95°F condensing temperature. 200 hp motor. Max pressure: 300 psi. Displacement: 445 cfm. Vi setting: 3.7. E.L. Nickell oil separator, Nat'l Bd: 20345, S/N: B-1242-B, MAWP: 300 psi @ 250°F, inside straight-wall dimensions: 1 ft 8 in. dia. x 5 ft. 5 in. Basco American Precision Industries Oil Cooler, S/N: 120621, Part No. 6A02A06108, shell side MAWP: 300 psi @ 300°F, tube side MAWP: 150 psi @ 300°F. Motor, 200 HP, 3550 rpm, 460 V, 60 Hz, 3 phase. Sullair Control Panel, Model: C16LA717-3.7, S/N: 056-01290. Max press: NH3-300 psig. Inlets: (1) 6 in. dia. port, (1) 4 in. dia. flanged port. Outlets: (1) 4 in. dia. flanged port, (2) 2 in. dia. port, (1) 2 in. dia. NPT fitting. Approximate weight: 5,100.







