

## Moyno Progressive Cavity Pump

Mfg: Moyno

Model: 2L10H SSQ

Stock No. CCFP073.

Serial No. AM21100

Moyno Progressing Cavity Pump. Model: 2L10H SSQ. S/N: AM21100. With 304 stainless steel suction housing, 316 stainless steel internal components, and nitrile rubber stator. Capacity: 125-150 gpm @ 80 psig and 0 psig, respectively. U.S. Motor, 10 hp, 1755 rpm, 230/460 V, 27.2/13.6 FLA (33.4/16.7 SFA), 60 Hz, 3 phase. U.S. Motors Varidrive Module, 450/3600 min/max rpm, 335 in-lbs max output torque. The Moyno progressing cavity pump is a single screw rotary pump. The pumping action is created by the single helical rotor rolling eccentrically in the double threaded helix of the stator. Inlets: (1) 6 in. dia. port with an 11 in. dia. flange and (8) 3/4 in. dia. attachment holes. Outlets: (1) 3 in. dia. threaded fitting with hex nut. Overall dimensions: 9 ft. 7 in. L x 21 in. W x 35-1/2 in. H.



