

V-Shaped Hopper with Screw Auger, Stainless Steel

Mfg:

Model:

Stock No. CCFP111.

Serial No.

V-shaped Hopper with Screw Auger. Stainless steel. Hopper dimensions: 92 in. L x 36 in. W x 30 in. H. Screw auger: 9 in. dia. Elektra motor: 1/2 hp, 1,725 rpm, 29 rpm output, 230/460 V, 2.4/1.2 amps, 60 Hz, 3 phase. Overall dimensions: 162 in. L x 48 in. W x 38 in. H.

