

Fristam FKL-50 Positive Displacement Pump - 10 HP

Mfg: Fristam

Model: FKL-50

Stock No.: CAGC1054

Serial No.: 007718

Fristam rotary lobe positive displacement pump. Model FKL-50. Serial: 007718. Max pressure: 300 PSI. Displacement per revolution: 0.097 gallons. Max flowrate: 58.2 gallons per minute at 600 RPM. GE Motor: 10 HP, 1755 RPM, 208-230/460V, 60 Hz, 3-phase, 215TCY frame. Nord gear reduction drive: 11.71 ratio (150 final RPM, 14.55 GPM). Stainless steel base. Ports: 3 in. clamp. (ACN80)



