

Fristam FKL-150 Positive Displacement Pump - 5 HP

Mfg: Fristam

Model: FKL150

Stock No.: CAGC1055

Serial No.: FKL1500601735

Fristam rotary lobe positive displacement pump. Model FKL-150. Serial FKL1500601735. Max pressure: 300 PSI. Displacement per revolution: 0.259 gallons. Max flowrate: 155.4 gallons per minute at 600 RPM. Baldor motor: 5 HP, 208-230/460V, 13.8-13/6.5 amps, 1750 RPM, 184TC frame, 60 Hz, 3-phase, TEFC. SEW-Eurodrive gear reduction drive: 11.88 ratio, 147 final RPM (38 GPM). Stainless steel base. Ports: 3 in. clamp. (ACN115)



