

Tri Clover Centrifugal Pump

Mfg: Tri Clover

Model: CS216MD14L-S

Stock No. CCFP503.

Serial No. J0088

Tri Clover Centrifugal Pump. Model CS216MD14L-S. S/N J0088. Capacity: up to 97 gpm. Impeller diameter: 4-1/2 in. Stainless Steel Electrical Motor, 1.5 hp, 1740 rpm, 230/460 V, 4.9/2.45 amps, 60 Hz. C-series pumps deliver dependable performance under any low-viscosity application. They feature a practical low maintenance design and can handle viscous products at elevated GPM and pressure ratings. Applications include: pharmaceutical, biotechnology, fine chemical, food and beverage industries. Inlets: (1) 2-1/2 in. Outlets: (1) 1-1/2 in. Overall dimensions: 20-1/2 in. L x 9 in. W x 11 in. H.

