

G & H Centrifugal Pump- 15 hp

Mfg: G&H

Model: GHH-30

Stock No. CCFP113.

Serial No. 97-3-53545

G & H Centrifugal Pump- 15 hp.

- Stainless steel head.
- Model: GHH-30.
- S/N: 97-3-53545.
- Pump has a 7-1/2 in. dia. impeller. Inlets/Outlets: (1) 2-1/2 in. S-Line connection and (1) 3 in. S-Line connection.
- 15 hp Lincoln Electric Motor, 3,940 rpm, 200/400 V, 44/22 amps, 60 Hz, 3-phase.
- Overall dimensions: 29 in. L x 15 in. W x 17 in. H.
- This pump does not have double mechanical seals with water flush.



