

Elliot Cherry Pitter

Mfg: Elliot

Model:

Stock No. CCFP304.

Serial No.

Elliot Cherry Pitter, Hopper dimensions 30 in. L x 20 in W x 11 in. H, Mesh size 3 (1/4 in. dia. openings), 50 in. long cherry pit exit narrows from 10 in. wide to 6 in. wide, 11.5 in. W. Product exit. 2 hp GE motor, 1,440 rpm, 220/440 V, 5.84/2.92 amps, 60 Hz, 3-phase, 4:1 pulley ratio. Overall dimensions: 68 in. L x 35 in. W x 72 in. H.



