

## Paddle Pulper/Finisher

**Mfg:**

**Model:**

**Stock No. CSWB159.2a**

**Serial No.:**

Paddle Pulper/Finisher. Paddle dimensions: (4) 17 in. L x 3 in. Lesson Electric Motor, 7-1/2 hp, 1760 rpm, 208-230/460 V, 20/10 amps, 60 Hz, 3 phase. Driver pulley diameter: 5 in. Driven pulley diameter: 9 in. Ratio: 1.8, 978 final rpm. Inlets: 11-1/2 in. W x 16 in. L. (hopper infeed). Outlets: (1) 3 in. dia. FNPT. (liquid discharge), (1) 3-1/2 in. W x 7-1/2 in. L. (pulp discharge). Overall dimensions: 4 ft. 9 in. L x 2 ft. 8 in. W x 4 ft. 2 in. H.



