

Elevated Auger Conveyor, Stainless Steel

Mfg:

Model:

Stock No. CCIS003

Serial No.

Elevated Auger Conveyor. Stainless steel. Auger: 90 in. L x 6 in. dia. with 6 in. thread pitch. Auger housing: 7 in. dia. Outlet: 5-1/2 in. Hopper: 18 in. L x 15 in. W. Gould Century Motor: 1 hp, 1750 rpm, 180-200/100 V, 4.90-.47/.94 amps. Gear ratio: 60:1, 29 final rpm, 1518 in.-lb. torque (output). Motor drive turns a 4-1/2 in. sprocket with chain. Conveyor mounted on frame with three legs on casters for easy positioning. Overall dimensions: 60 in. L x 87 in. W x 102 in. H.



