

Fristam Pump, Model FPX742-195

Mfg: Fristam

Model: FPX742-195

Stock No. DBBP2610.2

Serial No. FPX74298228

Fristam Pump. Model: FPX742-195. S/N: FPX74298228. Capacity: 51 gpm @ 110 psi and 253 tdh. Single mechanical seal. Baldor Industrial Motor, 10 hp, 3500 rpm, 208-230/460 V, 25.6-24/12 amps, 60 Hz, 3 phase. The FPX Series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations and is completely CIP'able. Inlet: 2-1/2 in. 'S' line, Outlet: 2 in. 'S' line. Overall dimensions: 27 in. L x 13 in. W x 12 in. H.



