

Fristam Centrifugal Pump

Mfg: Fristam

Model: FPX702-99

Stock No. DBBP2612.1a

Serial No. FPX70297932

Fristam Centrifugal Pump. Model: FPX702-99. S/N: FPX70297932. Capacity: 22.5 gpm @ 24 psi and 54 tdh. Single mechanical seal. Baldor motor, 2 hp, 3450 rpm, 208-230/460 V, 5.7-5.4/2.7 amps, 60 Hz, 3 phase. The FPX Series sanitary centrifugal pump has become an industry standard for most general applications. Capable of delivering high volumes and high pressures while handling shear sensitive products, it is the pump of choice for products with viscosities up to 600 cps and process temperatures up to 400°F. The FPX series is well known for quiet, efficient, low maintenance operations and is completely CIP'able. Inlet: 2 in. 'S' line. Outlet: 1-1/2 in. 'S' line. Overall dimensions: 30 in. L x 10 in. W x 8 in. H.



