

G & H GHH-Series Centrifugal Pump

Mfg: G & H

Model: GHH-40

Stock No. 12a.DBP6.1

Serial No. 96-3-52671

G & H GHH-Series Centrifugal Pump. Model: GHH-40. S/N: 96-3-52671. Sterling Electric Motor, 30 hp, 3525 rpm, 208-230/460 V, 76--68.4/34.2 amps, 60 Hz, 3 phase. The advanced impeller design results in unobstructed product flow and low NPSH requirements. Designed for CIP or manual cleaning. All product contact parts are constructed of AISI 316L stainless steel. Inlets: (1) 3 in. dia. S-line fitting. Outlets: (1) 2 in. dia. S-line fitting. Overall dimensions: 34-1/2 in. L x 17-1/2 in. W x 18 in. H.



