

General Machinery Corporation Hydraflaker Slicer

Mfg: General Machinery Corporation
Hydraflaker

Model: HYK 10/1

Stock No. DBPF2001.23

Serial No.

General Machinery Corporation Hydraflaker Slicer. Model: HYK 10/1. Rotating cutting drum dimensions: 13 in. dia. x 29 in. L. Maximum aperture/clearance: 30 in. L x 5-1/2 in. H. Cutting temperatures: 15 to 25 °F. Toshiba Motor, 10 hp, 1745 rpm, 230/460 V, 26.8/13.4 amps, 60 Hz, 3 phase. The Hydraflaker was designed for flaking/slicing of hard or frozen blocks of meat, poultry, fish, fruit, chocolate, vegetables, etc. It has a built in loading table with air-operated ram feed system. The rotating cutting drum avoids shredding or pulverizing product. Inlets: (1) 30 in. L x 5-1/2 in. H infeed. Outlets: (1) 30-1/2 in. L x 9 in. W discharge. Overall dimensions: 84-1/2 in. L x 40 in. W x 89 in. H.





