

Wanner Engineering Inc. Hydra-Cell Pumps

Mfg: Wanner Engineering Inc.

Model: D25MFCGHHEC

Stock No. DBPF2103.a

Serial No. 18537 and 19930

(2) Wanner Engineering Inc. Hydra-Cell Pumps. Model: D25MFCGHHEC. S/N's: 18537 and 19930. Capacity: 20 gpm at maximum pressure. Maximum pressure: 1000 psi. (2) Square D Pressure Switches. Previous duty: conveyor belt washer. Baldor Industrial Motor, 7-1/2 hp, 1725 rpm, 208-230/460 V, 21.5-20/10 amps, 60 Hz, 3 phase. Typical Hydra-Cell Pump features: seal-less compact design, durability and simplicity make Hydra-Cell pumps the optimum choice for handling aggressive fluids, abrasive fluids with particles, hot fluids, corrosive fluids, abrasives, wettable powders, cutting fluids, ultrapure fluids, adhesives, salt water, reclaim water, slurries, liquid gases, fertilizers, viscous fluids, chemicals, soap solutions. Skid mounted. Inlets: (4) 1 in. dia. NPT (male). Outlets: (1) 2 in. dia. NPT (male). Overall dimensions: 58 in. L x 37 in. W x 51 in. H.

