

Wanner Engineering Inc. Hydra-Cell Positive Displacement Pump

Mfg: Wanner Engineering Inc.

Model: H25X-FSGNNEH

Stock No: DBPF2261.2

Serial No: 67811

Wanner Engineering Inc. Hydra-Cell Positive Displacement Pump. Model: H25X-FSGNNEH. S/N: 67811. Flow rate for new pump is 20 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Lesson motor, 7.5 hp, 1750 rpm, 208-230/460 V, 20-18.4/9.2 amps, 60 Hz. Wanner's Hydra-Cell pumps feature: sealless compact design, and are the optimum choice for handling corrosive or abrasive fluids with particles, hot fluids, wettable powders, adhesives, salt water, reclaim water, slurries, liquid gases, fertilizers, soap solutions, and those with viscous properties. Stainless steel base. Inlets: (1) 2 in. dia. FNPT. Outlets: (1) 1-1/2 in. dia. FNPT. Overall dimensions: 3 ft. L x 1 ft. 9 in. W x 1 ft. 11 in. H.(ACN86).

