

Wanner Engineering Inc. Hydra-Cell Positive Displacement Pump

Mfg: Wanner Engineering Inc.

Model: H25X-FSGNNEH

Stock No. DBPF2261B.2

Serial No. 67812

Wanner Engineering Inc. Hydra-Cell Positive Displacement Pump. Model: H25X-FSGNNEH. S/N: 67812. Pump capacity: 33.33 gpm. Lesson motor, 7.5 hp, 1750 rpm, 208-230/460 V, 20-18.4/9.2 amps, 60 Hz. Typical Hydra-Cell Pump features: seal-less compact design, durability and simplicity make Hydra-Cell pumps the optimum choice for handling aggressive fluids, abrasive fluids with particles, hot fluids, corrosive fluids, abrasives, wettable powders, cutting fluids, ultrapure fluids, adhesives, salt water, reclaim water, slurries, liquid gases, fertilizers, viscous fluids, chemicals, soap solutions. Stainless steel base. Pump inlet: 2 in. threaded (female), outlet: 1-1/2 in. threaded (female). Overall dimensions: 36 in. L x 21 in. W x 23 in. H.

