

Sandpiper Containment Duty Diaphragm Pump

Mfg: Sandpiper

Model: ST1

Stock No. DCBJ205B.6

Serial No. _____

Sandpiper Containment Duty Diaphragm Pump. Model: ST1. Maximum capacity: 42 gpm. Displacement per stroke: 0.09 gal. Maximum solids handled: 1/4 in. Maximum discharge pressure: 125 psi. Containment duty pumps are ideal for highly corrosive and hazardous chemical fluid requirements. All CD duty pumps are exclusively designed with containment chambers, hydraulically balanced/coupled pumping diaphragm and driver diaphragm assemblies. CD pumps are constructed of aluminum, cast iron, stainless steel alloy 'C', polypropylene, and kynar with TPE. Inlets: (1) 1/4 in. dia. NPT (female, for quick connect air fitting), (1) 1 in. dia. NPT (female). Overall dimensions: 14 in. L x 11-1/2 in. W x 14 in. H.

