







COIL: ALL STEEL HOT DIP GALVANIZED
REFRIG: RECIRC. AMMONIA BOTTOM FEED
DEFROST: HOT GAS COIL & PAN
UNIT: CONSTRUCTED OF MILL FINISH GALV'D SHEET STEEL.
LEGS ARE REMOVABLE IF DESIRED.

10610	78	77	67	33 1/2	47 3/8	7 1/8
9310	69 1/2	68 1/2	58 1/2	29 1/4	47 3/8	7 1/8
8010	61	60	50	25	46 5/8	6 3/8
7310	57	56	45 3/4	22 7/8	46 5/8	6 3/8
6610	52 1/2	51 1/2	41 1/2	20 3/4	46 1/8	5 7/8
5910	48	47	37 1/4	18 5/8	46 1/8	5 7/8

UNIT CIRCUITED FOR 2 TO 1
RATE OF RECIRCULATION
WITH PUMPED LIQUID SUBCOOLED
TO EVAPORATOR REFRIGERANT.

5 HP. 1 0 R.P.M. 460/60/
APPROX. WT. 9800#
BTU/H 732000
CFM 86000
COIL TEMP. -38°F
ROOM TEMP. -25°F

TAG: BLAST FREEZER
③ REQ'D.

F.E.S. SOUTHWEST INC.
P.O.# KRK-0217

WORK TO DIMENSIONS
DO NOT SCALE PRINT

TOLERANCES
UNLESS OTHERWISE SPECIFIED FOLLOW:
ING TOLERANCES APPLY
FRACTIONAL ± 1/2
ONE PLACE DEC. (.0) ±
TWO PLACE DEC. (.00) ±
THREE PLACE DEC. (.000) ±
ANGULAR ±
TOLERANCES ARE NOT CUMULATIVE.

THIS DRAWING IS THE PROPERTY OF KRACK
CORP. AND IS SUBJECT TO RETURN UPON RE-
QUEST. IT IS TO BE USED ONLY FOR THE PUR-
POSE FOR WHICH IT WAS PREPARED.

F. V. SPM									
ASSY.			PROD.						
TOOL ROOM			CONN.						
FIN. PUNCH			COIL						
SHEET METAL			ENG.						
LOCATION		A	LOCATION		A	NO.	CHANGE DESCRIPTION	DATE	CHK'D.
PRINT DISTRIBUTION					REVISIONS				
MATERIAL AS SPEC.									
FINISH AS SPEC.			SUPERSEDES			SUPERSEDED BY			
DATE 1-26-84			SCALE			NO. REQ'D.			
DRAWN JEK			CHECKED			APPROVED			
TITLE CEILING TYPE AXIAL FLOW PRODUCT COOLER									
MOD.SPCHS10610-3-5 RBA HGU JOB NO. 337842									