

Stainless Steel Belt Conveyor Line

Mfg:

Model:

Stock No. DENF006.

Serial No.:

Stainless Steel Belt Conveyor Line. (2) 70 in. L x 25 in. W x 6 in. H sections, (1) 10 ft. 6-1/2 in. L x 25 in. W x 6 in. H section, and (1) 10 ft. 8 in. L x 41 in. W x 34 in. H. Baldor Industrial Motor, 1 hp, 1725 rpm, 208-230/460 V, 3.7-3.4/1.7 amps, 60 Hz, 3 phase. Motor Drive, 40 ratio, 43.125 rpm (final).



