

## Stainless Steel Frame Belt Conveyor

Mfg:

Model:

Stock No.: DNBA049

Serial No.:

(3) Stainless Steel Frame Belt Conveyor. Conveyor belt: Maximum aperture/clearance: 10 in. W x 7 in. H. Belt Dimension: 8 in. W x 2 ft 11 in. L. Baldor Industrial Electric Motor, 1/2 HP, 1725 RPM, 230/460 V, 1.5 AMPS, 60 Hz, 3 phase. Hub City gear reducer. Infeed/exit height: 4 ft. 6 in. Overall dimensions: 3 ft. L x 2 ft. 6 in. W x 5 ft. 4 in. H.



