

Stainless Steel Dough Roller Sheeter

Mfg:


Model:




Stock No.: DNBA214



Serial No.:

Stainless Steel Dough Roller Sheeter. Roller dimensions: (2) 8 in. dia. x 2 ft. L. (1) 12 in. dia. x 2 ft. L. Gap roller dimensions: 5/16 in. Second roller gap dimensions: 1/16 in. (2) Baldor Super-E motor, 10 hp, 1760 rpm, 230/460 V, 25/12.5 amps, 60 Hz, 3 phase. Nord gear drive, ratio: 87.06, rpm out: 20 (final), 2nd ratio: 53.83, rpm out: 32 (final). Inlets: (1) 2 ft. L x 1 ft. 10 in. W. (top infeed). Outlets: (1) 1 ft. 10 in. L x 1 ft. 1/2 in. W. (discharge). Overall dimensions: 9 ft. L x 2 ft. 9 in. W x 7 ft. 9 in. H.









Super-E
BALDOR
9A

Super-E
BALDOR
9A

LIST NO.		CONNECTION	
SPEED		LEAD	
PHASE		VOLTAGE	
SER.		H.P.	
VOLTS			
AMPS			
R.P.M.			
KZ.			
SER.F.			
NEMA NOM. EFF.			
RATING			
PLI. BRG.			

BALDOR
E BALDOR ELEC. CO. FT. SMITH, AR.
USA

