

## Warren Rupp Sandpiper® Air Powered Double Diaphragm Pump

**Mfg: Warren Rupp**

**Model: PB3/4-A**

**Stock No.: DNBA218**

**Serial No.: 543770**

Warren Rupp Sandpiper® Air Powered Double Diaphragm Pump. Model: PB3/4-A. S/N: 543770. Type: TR-3-PP. Approximate flow rate for new pump is 20 gpm with required air flow and pressure at 30 psi. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Polypropylene construction with Hytrel diaphragms, Hytrel ball valve. 416 stainless steel diaphragm rod, and 301/302 stainless steel hardware. MAWP: 100 psi (air), Temperature limits: 40°F min. and 150°F max. Inlets: (1) 1-1/2 in. dia. S-line fitting, (1) 1/4 in. dia. male quick connect fitting (air inlet). Outlets: (1) 1 in. dia. bevel seat w/hex nut, (1) 1/4 in. dia. FNPT fitting (exhaust). Overall dimensions: 1 ft. 9 in. L x 9-1/2 in. W x 1 ft. 7 in. H.(ACN6).



