

Frick Rotary Screw Compressor

Mfg: Frick

Model: RWB 54

Stock No. DPF1806.4a

Serial No.

Frick Rotary Screw Compressor. Model: RWB 54. Compressor run time: 05475 hrs. Refrigerant: R-717. Volume Ratio: 24, Max speed 3,600 rpm, MAWP 300 psig. Inlets/Outlets 4 in. dia. suction, (1) 4 in. dia. valve discharge. Baldor Industrial Motor: 250 hp, 3,550 rpm, 460 V, 275 amps, 60 Hz, 3 phase. Overall dimensions: 12 ft. L x 43 in. W x 77 in. H.

Frick Oil Separator, Nat'l Bd: 41556, shell thickness: .375, head thickness .32, MAWP 300 psig at -20 to 200 °F, mat'l SA: 53-S-B, mat'l TS: 60000. (2) Frick Oil Coolers, S/N's: MC78079 and MC78083, shell thickness: .277, head thickness: .75, radius: flat, MAWP 300 psig at -20 to 200 deg. F. Mat'l SA: 53-S-B, TS: 60000. Viking Positive Displacement Pump, Model: AS4195, S/N: 5009143, inlets/outlets: (2) 2-1/2 in. dia. NPT (female). Toshiba Motor, 3 hp, 1155 rpm, 230/460 V, 10/5.0 amps, 60 Hz, 3 phase. Starter included.



