

## 1994 Tri Clover Centrifugal Pump

**Mfg: Tri Clover**

**Model: C216MDG25T-S**

**Stock No: DPLS149.4**

**Serial No: 191191-01**

1994 Tri Clover Centrifugal Pump. Model: C216MDG25T-S. S/N: 191191-01. Impeller: 5-1/4 in. dia. Capacity: 240 gpm @ ~52 psi. Reliance Electric motor: 5 hp, 3510 rpm, 230/460 V, 38.8/19.4 amps, 60 Hz, 3 phase. ID No. 01MAF97907\_G001WW. Frame size: XO254IO. The C-Series pump is the original, all-purpose, sanitary process centrifugal pump. Its practical design and flexibility have provided processors with strong performances in thousands of applications. A great value, the C-series pump maintains an integral Clean-In-Place design as standard. Inlets: (1) 1 1/2 in. dia. s-line, (1) 1 in. dia. s-line. Outlets: (1) 2 1/2 in. dia. s-line. Overall dimensions: 2 ft. 7-5/8 in. L x 1 ft. 7 in. W x 1 ft. 4-1/4 in. H.





