

Transfer Inclined Cleated Conveyor

Mfg:

Model:

Stock No. DPFI312.a

Serial No.

Transfer Inclined Cleated Conveyor. Maximum aperture/clearance above belt: 18 in. W x 2 in. H. Height at conveyor inlet: 34 in. Height at conveyor outlet: 64 in. Effective belt length: 69 in. Infeed hopper dimensions: 20 in. L x 15 in. W. Product area between cleats: 135 in. sq. Stainless steel frame with (4) casters for easy positioning. Overall dimensions: 75 in. L x 38-1/2 in. W x 69 in. H.

