

Application Engineering Corporation Water-Cooled Chiller- 10 Ton

Mfg: Application Engineering Corporation

Model: WC-10-D/B

Stock No. DRGP067.8

Serial No. 76F053

Application Engineering Corporation Water-Cooled Chiller- 10 Ton. Model: WC-10-D/B. S/N: 76F053. Refrigerant: R-22. Heat transfer fluid: 30/70 antifreeze/water. Minimum temperature: 20/50 °F. System requirements: 230 V, 45 amps, 60 Hz, 3 phase. Copeland Copelmatic Compressor, Model: 9RC1-1010-THC, S/N: 81K78633, electrical requirements: 208/230 V, 208 RLA, 60 Hz, 3 phase. Inlets: (1) 1 in. dia. NPT (female, process), (1) 1 in. dia. NPT (female, condenser). Outlets: (1) 1 in. dia. NPT (female, process), (1) 1 in. dia. NPT (female, condenser). Overall dimensions: 62 in. L x 33 in. W x 52 in. H. Standard Refrigeration Company Shell and Tube Condenser, Model: HX10, shell design pressure: 250 psi, test pressure: 225 psi.



