

2000 Tri Clover Tri-Blender

Mfg: Tri Clover


Model: F1114LMDG-1129-10

Stock No: DPPX41527.24

Serial No: 511626-01

Tri Clover Tri-Blender. Model: F1114LMDG-1129-10. Maximum output capacity: 10 gpm. Dry product addition rate up to 25 lbs/min (feed rate is 8-10 gpm). Maximum product viscosity: 500 centipoises, maximum product temperature: 160°F. Reliance Electric Motor, 3 hp, 3515 rpm, 230/460 V, 7.6/3.8 amps, 60 Hz, 3 phase. Inlets: (1) 14-1/2 in. dia. (hopper infeed). Outlets: (1) 1 in. dia. S-line fittings, (1) 1-1/2 in. dia. S-line fittings. Overall dimensions: 1 ft. 2 in. L x 1 ft. 2 in. W x 4 ft. 4 in. H.







ELECTRIC
DUTY MASTER®

TYPE	DESIGN	IDENTIFICATION NO		
P	B	01UBZ8077501 G		
REV	VOLTS	AMPS	HZ	
315	230	7.6	60	
315	460	3.8	60	
290	220	8.1	50	
290	380	4.7	50	

STD 21 1/1/79 MOTOR WEIGHT 94 LBS
DIP. D.E. BEARING 25BC02JPP30A
ELECTRIC INDUSTRIAL CO. PLANT 6