

Vertical Lift Incline Conveyor

Mfg:

Model:

Stock No. DSB1127.3

Serial No.

Vertical Lift Incline Conveyor. Maximum aperture/clearance above belt: 16-1/2 in. W x 4 in. H. Baldor Washdown Duty Motor, 1/2 hp, 1725 rpm, 208/460 V, 1.6/0.8 amps, 60 Hz, 3 phase. Dayton Motor Drive, 60:1 ratio, 28.75 rpm (final). Inlets: (1) 32 in. W x 12 in. H in-feed hopper. Overall dimensions: 17 ft. L x 36 in. W x 43 in. H.

