

Pneumatic Single Piston Filler- 24 Fl. Oz

Mfg:

Model:

Stock No. DSBI197.8a

Serial No.

Pneumatic Single Piston Filler- 24 Fl. Oz. Hopper dimensions: 2 ft. dia. x 10 in. H. Capacity: 19 gal. Piston dimensions: 3 in. dia. x 1 in. W. Cylinder dimensions: 3 in. dia. x 7 in. L. Adjustable piston travel. Unit is equipped with a foot switch for cycle initiation. Dimension from base to discharge port (adjustable): 6-7/8 in. V-Block product holder: 5 in. W x 4 in. H. Air supply controlled by Wilkerson filter-regulator-lubricator. Unit mounted on (4) casters for easy positioning. Outlet: (1) 3/8 in. dia. discharge port. Overall dimensions: 4 ft. 4 in. L x 4 ft. 6 in. W x 6 ft. H.



