

Crane Deming Centrifugal Pump

Mfg: Crane Deming

Model: 4066 80651201

Stock No. DTTC2017.

Serial No. DC-900689

Crane Deming Centrifugal Pump. Model: 4066 80651201. S/N: DC-900689. Type: A1. Size: 8x8x12. Unit: RH. (Semi-open) impeller diameter: 10 ½ in. Capacity: 1400gpm. Baldor Industrial Motor, 50 hp, 1775 rpm, 230/460 V, 114/57 amps, 60 Hz, 3 phase. Inlets/outlets: (2) 8 in. dia. flanged ports, (suction and discharge). Crane Deming centrifugal pumps are frame mounted with back, pull-out designs and semi-open impellers. Applications include: water, abrasive liquids, acids and oils with uses in a variety of industrial services to include: irrigation, pollution control and cooling towers. Overall dimensions: 5 ft. 1 in. L x 3 ft. W x 2 ft. 1 in. H.





