

Pneumatic Single Piston Filler- 24 Fl. oz. with Hopper

Mfg:	Model:
Stock No. DSBI198.8a	Serial No.

Pneumatic Single Piston Filler- 24 Fl. oz. Hopper dimensions: 2 ft. dia. x 10 in. H. Capacity: 19 gal. Piston dimensions: 3 in. dia. x 1 in. W. Cylinder dimensions: 3 in. dia. x 7 in. L. Adjustable piston travel. Conveyor infeed/exit height: 3 ft. 6 in. Maximum aperture/clearance: 5 in. W x 8 in. H. Air supply controlled by Wilkerson filter-regulator-lubricator. Unit mounted on (4) casters for easy positioning. Outlet: (1) 3/8 in. dia. discharge port. Overall dimensions: 5 ft. L x 4 ft. 6 in. W x 6 ft. 4 in. H.







