

2000 Waukesha Model 320 Positive Displacement Pump

Mfg: Waukesha

Model: 320 U1

Stock No: DTTC2020

Serial No: 275433-00

2000 Waukesha Positive Displacement Pump. Model: 320 U1. S/N: 275433-00. Flow rate for new pump is 450 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Features include: ease of cleaning and disassembly, three-way mounting options, and non-galling, Waukesha "88" alloy rotors. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. 316 stainless steel pump body, cover and shaft. Speed reducer gear ratio: 4:1:1, final speed: 427 rpm. Seal option: John Crane #8-B2, carbon/ceramic, Viton elastomers. Baldor industrial motor, 25 hp, 1750 rpm, 230/460 V, 40/30 amps, 60 Hz, 3 phase. This pump complies with FDA standards and design conforms with 3A, USDA ISO 9001:2000 and CE standards. Low to high product viscosity applications include: batters, fruit fillings, juices, pastes, soups, dressings, ground meats, syrups and extracts. Absence of bearing and rotor to rotor contact ensures adequate handling of non-lubricating fluids and fluids with abrasive qualities. Inlets/outlets: (2) 6 in. dia. flanged ports. Overall dimensions: 4 ft. 9 in. L x 2 ft. 6 in. W x 3 ft. 10 in. H.(ACN314).





