

Stainless Steel Hydraulic Power Pack

Mfg:

Model:

Stock No. DTTC2081.

Serial No.:

Stainless Steel Hydraulic Power Pack. Food grade hydraulic oil only. Stainless Steel Tank- 90 Gallon. Dimensions: 3 ft. L x 1 ft. 8 in. W x 2 ft. 5 in. H. Vescor Hydraulic Pump with Baldor Electric Motor, 15 hp, 1765 rpm, 230/460 V, 37/18.5 amps, 60 Hz, 3 phase. Vickers Relief Valve, S/N: CT 10 B30, pressure range (min/max): 125/1000 psi. Overall dimensions: 4 ft. 4 in. L x 2 ft. 10 in. W x 5 ft. 7-1/2 in. H.





Super-E
SUPER-EFFICIENT INDUSTRIAL MOTOR
BALDOR FT. SMITH, AR. MFG. IN U.S.A.

CAT. NO.	18000000000000000000		
SPEC.	18000000000000000000		
HP	1/2		
VOLTS	208/240V		
AMPS	1.7/1.5		
R.P.M.	1725		
FRAME	254T	RZ	ON
SER. F.	CODE	DES	CLASS
NEMA NOM. EFF.	0.76	4	RF
RATING	AMB		
CC	USABLE AT 208V		
BEARINGS	DE	ODE	6210
ENCL.	18000000000000000000		

UL E