

1999 Vertical Air Receiver Tank- 1000 Gallon

Mfg:

Model:

Stock No. DTWA094.3

Serial No.:

1999 Vertical Air Receiver Tank- 1000 Gallon. Nat'l Bd: 208494. MAWP: 155 psi at 400 °F. MDMT: -20 °F at 155 psi. Head thickness: 0.218 in. Shell thickness: 0.250 in. Oval manway: 15 in. L x 11-1/2 in. W. Tank dimensions: 50 in. diameter x 10 ft. H. Air inlet/outlet: 2 in. pipe, flange: 11 in. diameter, (8) attachment holes, center to center: 10 in. Tank humidity discharge valves: 3/4 in. pipe. Overall dimension: 60 in. diameter x 12 ft. 11 in. H.

