


Pallet Stretch Wrap Machine

| | |
|----------------------------|--------------------|
| Mfg: | Model: |
| Stock No. DTTC2061. | Serial No.: |

Pallet Stretch Wrap Machine. Stainless steel frame. Rotating arm radius: 5 ft. Baldor Industrial Motor (revolving arm assembly), $\frac{3}{4}$ hp, 1750 rpm, 180 V, 5.7 amps. Browning Gear Drive, 63 ratio, 27.7 rpm (final). Reliance Electric Motor (revolving arm assembly), $\frac{1}{2}$ hp, 2500 rpm, 90 V, 5.0 amps. Boston Gear Drive. Leeson Electric Motor (roll assembly), $\frac{1}{2}$ hp, 1750 rpm, 90 V, 5.0 amps. Grove Gear OE Series Speed Reducer, 5 ratio, 350 rpm (final). Overall dimensions (roll assembly): 2 ft. 7 in. L x 1 ft. W x 7 ft. 3 $\frac{1}{2}$ in. H. Overall dimensions (revolving arm assembly): 9 ft. 9 in. L x 2 ft. 4 in. W x 4 ft. 6 in. H. Overall dimensions (frame supports): 7 ft. 9 in. L x 1 ft. 4 in. W x 10 ft. 2 in. H.









Stainless Steel Control Panel. Overall dimensions: 3 ft. 11 in. L x 1 ft. 5 in. W x 6ft. 9 in. H

