

FES 575 / Mycom 250LUD-ME Screw Compressor Package - 700 hp

Mfg: FES Mycom

Model: 575B / 250LUD-ME

Stock No: DTTC832

Serial No: 2512613

FES 575 / Mycom 250LUD-ME Screw Compressor Package. Model: 575 / 250LUD-ME. S/N: 2512613. Job No: 560-18752. Refrigerant: R-717, ammonia. Leak test pressure: 313 psig. Vi setting: 3.6. Displacement: 853 cfm. Hydrostatic test pressure: 470 psig. FES oil separator, S/N: 88106, Nat'l Bd: 3464, MAWP: 250 psi at 200 °F. Viking rotary pump, Model: AL4195, S/N: 11677751. Reliance Electric motor, 7-1/2 hp, 1175 rpm, 230/460 V, 20.4/10.2 amps, 60 Hz, 3 phase. FES Micro II control panel, 120 V. General Electric motor, 700 hp, 3570 rpm, 4160 V, 86.3 amps, 60 Hz, 3 phase. Inlets: (1) 14 in. dia. refrigerant suction port with a 17 in. dia. flange. Outlets: (1) 5 in. dia. refrigerant discharge tube. Overall dimensions: 13 ft. 1 in. L x 4 ft. 8 in. W x 8 ft. 4 in. H. Compressor run time: 7,375 hrs. since rebuild. (SR450) (ACN950).





