

Fristam FM Series Centrifugal Pump

Mfg: Fristam

Model: FM342-165

Stock No: ENDX188717.12a

Serial No: FM342013165

Fristam FM Series Centrifugal Pump. Model: FM342-165. S/N: FM342013165. Flow rate for new pump is 200 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Baldor motor: 40 hp, 3540 rpm, 230/460 volts, 88/44 amps, 60 Hz, 3 phase. Overall (1) 2-1/2 in. s-line inlet. (1) 2-1/2 in. s-line outlet. (1) 5/8 in. shut off MNPT valve water flushed inlet/outlet. (1) 3/8 in. FNPT inlet/outlet. dimensions: 5 ft. 4-1/2 in. L. x 1 ft. 10-1/2 in. W. x 1 ft. 10-3/8 in. H.(ACN214).



