

Stainless Steel Wash Conveyor with Filtered Hopper

Mfg:

Model:

Stock No: DWKN02

Serial No:

Stainless Steel Wash Tanks with Flat Wire Chain Conveyor. Chain width: 3 ft. Gap between links: 0.55 in. Thickness of flat wire: 0.045 in. Rod diameter: 0.120 in. Pitch: 0.56 in. Reliance Electric Motor, 2 hp, 172 rpm, 208-230/460 V, 6.4/3.2 amps, 60 Hz, 3 phase. Speed Reducer. Drain pan dimensions: 17 ft. 4 in. L x 3 ft. 6 in. W. Inlets: (1) 1-1/2 in. dia. FNPT (wash fluid), (1) 2 in. dia. FNPT (wash fluid). Outlets: (1) 2 ft. L x 2 ft. W product discharge port. Overall dimensions: 20 ft. 11 in. L x 4 ft. 3 in. W x 9 ft. H.

Stainless Steel Filter Hoppers. Mesh dimensions: 2 ft. 6 in. L x 2 ft. 5-1/2 in. W. Hole diameter: 1/2 in. Inlets: (1) 2 ft. 6 in. L x 2 ft. 5-1/2 in. W product infeed. Outlets: (1) 2-1/2 in. dia. drain port, (1) 20 in. W x 6 in. H tilt discharge (solids). Overall dimensions: 3 ft. 4 in. L x 3 ft. 4 in. W x 3 ft. H.











