

Ampco Centrifugal Pump D-series

Mfg: Ampco

Model: DC2

Stock No. ENDX676.1a

Serial No. CC-19071-1-1

Ampco Centrifugal Pump D-series. Model: DC2. S/N: CC-19070-1-1. Size: 3 x 2 ½. Capacity: 300 gpm @ 40 tdh (17 psi using specific gravity of water = 1). Impeller diameter: 4 ½ in. Baldor Industrial Motor: 7.5 hp, 3450 rpm (final), 575 V, 7.2 amps, 60 Hz, 3 phase. Principally for CIP and COP systems, its efficient performance, quiet operation, and low maintenance requirements make Ampco's DC2 the preferred pump in the CIP/COP market. Inlets: (1) 3 in. dia. S-line fittings. Outlets: (1) 2 ½ in. dia. S-line fittings. Overall dimensions: 2 ft. 1 in. in. L x 1 ft. 1 in. W x 11-½ in. H.



