

## Alfa Laval Contherm 2-Barrel Scrape Surface Heat Exchanger

Mfg: Alfa Laval

Model: 6X9

Stock No. EECA002.

Serial No. C1041NPC

Alfa Laval Contherm 2-Barrel Scrape Surface Heat Exchanger. Model: 6x9. S/N: C1041NPC. Uses (14) 10-1/2 in. L x 1-5/8 in. W staggered scraper blades per rotor. Goulds Century Motor, 20 hp, 1160 rpm, 230/460 V, 56/28 amps, 60 Hz, 3phase. Reliance Electric Motor. The horizontally-mounted Alfa Laval Contherm is a scraped surface heat exchanger consisting of a heat transfer cylinder and a rotor with attached scraping blades. The product is pumped into the lower end of the Contherm heat exchange cylinder. As it flows through the cylinder, it is continuously removed from the cylinder's precisely finished walls by the scraping blades. Each rotor will turn at a final speed of 255 rpm. Inlets: (2) 1-1/2 in flanged fittings (media), (2) 2 in. dia. S-line fittings. Outlets: (2) 1-1/2 in flanged fittings (media), (2) 2 in. dia. S-line fittings. Overall dimensions: 89 in. L x 65 in. W x 72 in. H.



