

Kramer CTT Thermobank Condensing System- 5 Ton

Mfg: Kramer

Model: CTT20500M22

Stock No. FRGW001D.

Serial No. M0069365-012

Kramer CTT Thermobank Condensing System- 5 Ton. Model: CTT20500M22. S/N: M0069365-012. Medium temperature. Refrigerant: R-22. Copeland Discus Compressor, 5 hp, 380-420/460V, 10.5 FLA, 3 ph @ 50/60 Hz. (2) Marathon Electric Motors, 1/2 hp, 1075 rpm, 460 V, 2.4 FLA, 60 Hz, single phase. (2) 3 blade fans, 8 in. L x 6 in. W fan blades. General Electric Transformer, class: 180, 0.750 kVA, 400 AMB, 60 Hz, 100c rise. Ranco pressure gauge cut off, and (2) Ranco fan control switches. The Thermobank delivers more refrigeration with less energy consumption, less equipment, less installation and lower operating cost. Thermobank is available for all commercial and industrial applications. Less equipment is needed with Thermobank because it does more refrigeration in 24 hours than any other package system and also has the fastest defrost period (typically 5 to 10 minutes). Inlets: (1) 1 in. port. Outlets: (1) 1/2 in. port. Overall dimensions: 68 in. L x 47 in. W x 62 in. H.



